

Category 8 6C Outlet



Category 8 6C outlet (SEKei6-45bk)

This Category 8 outlet is perfect for use with "6C" 25 x 38 faceplates and POD/GOP boxes.

Features

- Transmission performance in compliance with the ANSI/TIA 568-C.2-1 specifications for Category 8 cabling systems (i. e. suitable for runs of 5 – 30 metres)
- Provides quick and easy tool-less lever "butterfly style" termination
- Compliant with IEC60512-99-001 – suitable for use with IEEE 802.3at (PoE+) applications
- Suitable for 0.51 – 0.65mm/ 22 – 24 AWG stranded and solid wire
- Angled presentation minimizes issues with bend radius
- Window and paper labelling facility

Specifications

- Weight: 32 grams approx.
- Colour: Black and silver (faceplate adaptor is also available in white)
- Dimensions: 43 x 25 x 44 mm approx.
- Materials:
 - Socket housing: nickel-plated die-cast zinc
 - RJ45 contacts: 50µ"/1.27 µm gold-plated phosphor bronze
 - IDC contacts: tin-plated phosphor bronze
 - Tape: copper foil
 - Faceplate adaptor: ABS UL94-V0
- Supplied with hinged shutter, to reduce dust ingress, and a cable tie.
- Supplied as a kit.
- Packaging: In individual poly bag with instructions, then bagged in 20's
- EAN number: 5055386506573

Category 8 “Euro” Outlet



Category 8 “Euro” outlet, white (SEKei-45wh)

This Category 8 outlet is designed for use with “Euro” faceplates with 25 x 50 mm openings.

Features

- Transmission performance in compliance with the ANSI/TIA 568-C.2-1 specifications for Category 8 cabling systems (i.e. suitable for runs of 5 – 30 metres)
- Provides quick and easy tool-less lever “butterfly style” termination
- Compliant with IEC60512-99-001 – suitable for use with IEEE 802.3at (PoE+) applications
- Angled presentation minimizes issues with bend radius
- Supplied with a shuttered front aperture to reduce dust ingress
- Suitable for 0.51 – 0.65 mm/ 22 – 24 AWG stranded and solid wire
- Window and paper labelling facility

Specifications

- Weight: 36 grams
- Colour: White and silver (faceplate adaptor also available in black, to order)
- Dimensions: 53 x 40 x 25 mm
- Materials:
 - Socket housing: nickel-plated die-cast zinc
 - RJ45 contacts: 50µm/1.27 µm gold-plated phosphor bronze
 - IDC contacts: tin-plated phosphor bronze
 - Tape: copper foil
 - Faceplate adaptor: ABS UL94-V0
- Supplied with cable tie and supplied as a kit
- Packaging: In individual poly bag with instructions, then bagged in 20's
- EAN number: 5055386506566