


**EAO AG**

Tannwaldstrasse 88

4600 Olten

Switzerland

**Phone:** +41 62 286 9111

[info@eao.com](mailto:info@eao.com)

## Part No. 45-1530.2920.000.402, Mushroom-Head Pushbutton


[Specifications](#) | [Bill of Materials](#)

### Specifications

Actuator	<u>Mushroom pushbutton</u>
Lens Colour	Red
Function	2 Positions, maintained, pull release (O+l)
Housing Material	Metal
Shape of Handle or Frontring	Diameter 40 mm
Lock System	None
Key	None
Key Type	None
Switching Angle	None
Contacts	1NC
Terminal	Spring-loaded terminal
Voltage Illumination	None

Mounting Type	Front mounting
Mounting Style	Holder
Environmental Rating	IP66, IP67, IP69K
Industry Standards/Certifications	UL, CSA, VDE, CCC, CE, RoHS
Switching Function	On-Off
Illumination	None
Contact Material	Silver
Termination Style	Spring type
Mechanical Life	Maintain 500'000 switching cycles Momentary 1'000'000 switching cycles
AC Voltage	500 V
DC Voltage	500 V
Switching Current	10 A

## Bill of Materials

Actuator	45-2530.2920.000
Holder	45-2300.2000.000
Switch Element 1	45-312.1Z40