

**EAO AG**

Tannwaldstrasse 88

4600 Olten

Switzerland

**Phone:** +41 62 286 9111[info@eao.com](mailto:info@eao.com)

## Part No. 45-1231.11N6.000.401, Illuminated Pushbutton

[Specifications](#) | [Bill of Materials](#)

### Specifications

Actuator	<u>Illuminated pushbutton</u>
Lens Colour	White, transparent
Function	2 Positions, momentary (O<l)
Housing Material	Plastic
Shape of Handle or Frontring	raised/ level to bezel
Lock System	None
Key	None
Key Type	None
Switching Angle	None
Contacts	1NO
Terminal	Spring-loaded terminal
Voltage Illumination	24V AC/DC

Mounting Type	Front mounting
Mounting Style	Holder
Environmental Rating	IP66, IP67, IP69K
Industry Standards/Certifications	UL, CSA, VDE, CCC, CE, RoHS
Switching Function	On-Off
Illumination	White
Contact Material	Silver
Termination Style	Spring type
Mechanical Life	Maintain 500'000 switching cycles Momentary 3'000'000 switching cycles
AC Voltage	500 V
DC Voltage	500 V
Switching Current	10 A

## Bill of Materials

Actuator	45-2231.11N0.000
Holder	45-2300.1000.000
Switch Element 1	45-311.1Z40
LED Module	45-320.1N46