

**ModuPlug  
HDC MHP100 M 35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Type	HDC MHP100 M 35
Order No.	<a href="#">1435780000</a>
Version	Male, silver, 35 mm <sup>2</sup>
GTIN (EAN)	4050118240672
Qty.	10 pc(s).

## Data sheet

### ModuPlug HDC MHP100 M 35

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Net weight	16.24 g
------------	---------

### Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

### General data

Cross-section for connected wire	35 mm <sup>2</sup>	Material	Copper alloy
Production methods	turned	Stripping length, rated connection	19 mm
Surface finish	silver	Type	Male
Type of connection	Crimp connection		

### Classifications

ETIM 5.0	EC000796	ETIM 6.0	EC000796
eClass 6.2	27-26-12-02	eClass 9.1	27-44-02-04

### Approvals

ROHS	Conform
------	---------

### Downloads

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN</a>

**ModuPlug  
HDC MHP100 M 35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Accessories**

**... for compression cable lugs (acc. to DIN 46235)**



**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

**General ordering data**

Type	Order No.	Version	GTIN (EAN)	Qty.
ES MTR110 HEX 16/35	<a href="#">1500950000</a>		4050118309492	1 pc(s).

**Tools**



**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

**General ordering data**

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	MTR 110	<a href="#">9018020000</a>	Crimping tool, Crimping tool, universal hand presses, 6mm <sup>2</sup> , 120mm <sup>2</sup>	4008190064150	1 pc(s).
EPG 45		<a href="#">1500830000</a>	Crimping tool, 6mm <sup>2</sup> , 150mm <sup>2</sup>		4050118309317 1 pc(s).