HVAC CLAMP METER WITH DIFFERENTIAL TEMPERATURE

CL450



KLEIN EST TOOLS

THE GAME CHANGER IS HERE!

The dual-display **CL450 HVAC Clamp Meter** is a game changer for the HVAC professional. This True RMS, CAT IV meter offers DC microamps, differential temperature, digital temperature calibration, inrush current, and many other easy to perform functions for key HVAC applications.



- Measures DC current across the flame sensor
- Confirms flame rectification



- Dual display reads T1 and T2 measurements as well as displays the differential temperature
- Used to troubleshoot many HVAC applications



- Measures surge when electrical device is started up
- Critical for the installation, diagnostics and maintenance of electrical motors



- Temperature calibration corrections in field with a push of a button
- No more adjusting the potentiometer with a screwdriver

HVAC CLAMP METER WITH DIFFERENTIAL TEMPERATURE

CL450

HVAC\R

Measurement		
AC/DC Voltage	$ \overline{\widetilde{v}} $	1000V
AC + DC Voltage	v+v	•
AC Current	\widetilde{A}	600A
Resistance	Ω	60MΩ
DC Millivolts	mV	•
DC Microamps	μĀ	•
True RMS	TRMS	•
Non-Contact Voltage Testing	NCV	•
Low-Pass Filter	LPF	•
Low Impedance	LOW Z	•
Audible Continuity	•)))	•
Backlight		•
Differential Temperature	°F ℃ T2-T1	-40° - 1832°F (-40° - 1000°C)
Digital Temperature Calibration	T-CRL	•
Auto-Ranging	AUTO	•
Range Hold	RANGE	•
Data Hold	HOLD	•
Diode Test	+	•
Capacitance Test	16	•
Frequency/Duty Cycle	Hz%	•
Max/Min Value	MAX/ MIN	•
Relative Mode	$ \Delta $	•
Auto Power-Off	APO	•
LCD Display Count	6000	6000
Durability		
Drop Protection	N.	6.6 ft. (2 m)
Outal Ball	A	CAT IV 600V
Safety Rating	<u> </u>	CAT III 1000V



HVAC CLAMP METER WITH DIFFERENTIAL TEMPERATURE

CL450





Thermocouples are NOT intended for use on people or animals.

mormosoupros are ner mismasa for ass on people of ammais.			
Cat. No.	UPC# 0-92644+	Description I	Includes
CL450	69063-1	HVAC Clamp Meter w/ Differential Temperature	Carrying case, test leads, 2 thermocouples, 3 AAA batteries.
Accessori	es		
Cat. No.	UPC# 0-92644+	Description	Temprature Range
69435	69230-7	Replacement K-Type Thermocouple	-30 to 482° F
69140	69067-9	K-Type Temperature Pipe Clamp w/ Adapter	-4 to 212° F
69142	69068-6	High Temperature K-Type Thermocouple w/ A	Adapter 32 to 896° F
69144	69069-3	K-Type Temperature Probe w/ Adapter& Case	e -58 to 1112° F
69146	69070-9	Adapter, K-Type to Banana Plug	n/a
69417	69417-2	Magnetic Hanger	n/a

See our complete line of Test & Measure and HVAC products

www.kleintools.com







