

## LM4221H Laminator

The Aurora LM4221H is a reliable laminator that can laminate documents up to A4 in size. It has two adjustable temperature settings, one for 80-100 micron pouches and another for 125-150 micron pouches. It has a 4-6 minute warm up time and pull down entry and exit trays to make laminating your document easy. There is a user friendly jam release lever so that any problem laminations can be easily removed and the design of the laminator also incorporates a carry handle and cable tidy. The LM4221H is a great laminator for the home or office and includes two free A4 laminating pouches.



Temperature Adjustment



Integrated handle and cable tidy



Roller release mechanism

- A4 hot laminator
- Adjustable temperature settings
- 80-150 micron pouches
- Warm up time 4-6 minutes
- Jam release lever
- Integrated carry handle
- Integrated cable tidy



Colour options available to order (MOQ's apply)

Technical Specifications	
Laminator Size	A4
Laminating Method	Heat
Carrier Free Operation	Yes
Warm Up Time	4-6 mins
Heated Rollers	2
Pouch Size	ID to A4
Maximum Pouch Width	235mm
Pouch Thickness	80-150 Micron (X2)
Maximum Document Thickness	0.4mm
Laminating Speed	30 cm/minute
Jam Release Lever	Yes
Adjustable Temperature Setting	Yes (2 settings)
Entry Tray	Yes
Exit Tray	Yes
Integrated Carry Handle	Yes
Integrated Cable Tidy	Yes
Power LED Indicator	Yes
Ready LED Indicator	Yes
Machine Size (mm)	383x136x85mm
Machine Weight (kg)	1.7kg

Packaging	Unit Gift Box	Master Carton
Quantity	1	4
Dimensions (mm)	425x119x170	448x255x375
Weight (Kg)	1.92	9.0
Barcode	6925781430492	6925781430508

**Available from:**