



datasheet for PRUEF 2 S
 article number: 973659101



product description:	order number: 973 659-101
description:	Contact-protected test probe with elastic, shatter-proof insulating sleeve and slender stainless steel tip. Tip penetrates insulation and oxide layers. Insulated brass 4 mm diameter socket connection. Connects with sliding sleeve measuring leads. Accessory tip protector and IC tap SS 260.
typ:	PRUEF 2 S rot / red
system:	4mm sliding sleeve system
order number:	973 659-101
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	2 mm
type of contact:	test tip (unsprung)
type of termination:	4 mm socket (unsprung)
rated voltage:	30 VAC / 60 VDC
contact resistance:	10 mOhm
material	
contact material:	tip: stainless steel socket: brass
contact surface material:	tip: nickel
housing material:	PP / TPE
environmental conditions:	
temperature range:	-25 °C to +80 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	

