

RSB, Film, Metallized Polyester Stacked, Automotive Grade, 0.015 uF, 10%, 500 VDC, 85C, Lead Spacing = 5mm



| Dimensions | |
|------------|-----------------|
| L | 7.2mm +0.3mm |
| H | 11mm +0.1mm |
| T | 6mm +0.2mm |
| S | 5mm +/-0.4mm |
| LL | 17mm +1/-2mm |
| F | 0.6mm +/-0.05mm |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 1000 |

| General Information | |
|---------------------|---|
| Supplier: | KEMET |
| Series: | RSB |
| Dielectric: | Metallized Polyester Stacked |
| Style: | Radial |
| Features: | Automotive Grade, DC Multipurpose Applications |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Qualifications: | AEC-Q200 |
| AEC-Q200: | Yes |
| Miscellaneous: | Above 85C DC And AC Voltage Derating Is 1.25%/C |

| Specifications | |
|------------------------|---------------------------------------|
| Capacitance: | 0.015 uF |
| Capacitance Tolerance: | 10% |
| Voltage AC: | 220 VAC |
| Voltage DC: | 500 VDC |
| Temperature Range: | -55/+125C |
| Rated Temperature: | 85C |
| Dissipation Factor: | 0.80% 1kHz, 1.20% 10kHz, 2.50% 100kHz |
| Insulation Resistance: | 30 GOhms |
| Max dV/dt: | 700 V/us |
| Inductance: | 7 nH |