



Quality Products. Service Excellence.

Adjustable Depth 4-Post Rack Mount Shelf *RMA Series*

Up to 200 lbs Weight Capacity

Note: This product line will soon be discontinued as a stocked series. Available while quantities last. It has been replaced with **ADS Series**. For alternative solution assistance, please contact Hammond Customer Service - sales@hammfg.com or USA (716) 630-7030, Canada and International (519) 822-2960.

Features



- Constructed of 14-Gauge Steel.
- Adjustable mounting depth.
- Choice of vented or solid options.
- Mounts to both front and rear rails.
 - Requires two (2) pairs of rails.
- Finished in a rugged textured powder paint finish
- Includes all mounting hardware
- RoHS and REACH compliant.
- Manufactured in North America.



Accessories

- Mounting Hardware



Light Duty Shelves

Part No.	Shelf Type	Overall Shelf Depth	Adjustable Depth Range		Rack Units	Replaced by Part No.
			Min	Max		
RMASV1917BK1	Vented	17.00	17.00	27.00	1U	ADSV1825BK
RMASV1925BK1	Vented	25.00	25.00	35.00	1U	ADSV2536BK

Suggested Load Capacity of 75 lbs

Heavy Duty Shelves

Part No.	Shelf Type	Overall Shelf Depth	Adjustable Depth Range		Rack Units	Replaced by Part No.
			Min	Max		
RMASUHD1917BK1	Solid	17.00	17.00	27.00	2U	ADSV1825BK
RMASUHD1925BK1	Solid	25.00	25.00	35.00	2U	ADSV2536BK
RMASUHD1936BK1	Solid	36.00	36.00	48.00	2U	ADSV3642BK
RMASVHD1917BK1	Vented	17.00	17.00	27.00	2U	ADSV1825BK

Part No.	Shelf Type	Overall Shelf Depth	Adjustable Depth Range		Rack Units	Replaced by Part No.
			Min	Max		
RMASVHD1925BK1	Vented	25.00	25.00	35.00	2U	ADSV2536BK
RMASVHD1936BK1	Vented	36.00	36.00	48.00	2U	ADSV3642BK

Suggested Load Capacity of 200 lbs

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.