



ProStrip 10/20 Wire Strippers

P/N 15003C

Designed to meet the demanding expectations of professionals. These wire strippers deliver performance, comfort and consistent, reliable results. The tools can be used left or right handed - wire sizes are marked on both sides. Ergonomically designed handles require less hand force. The curved cutting blades ensure cleaner, precise cuts. Color-coded for quick identification.

- For 10-20 AWG solid / 12-22 AWG stranded wire.
- Precision-ground strip nest.
- Cut and chase threads on 16/32 & 8/32 bolts.
- Serrated plier nose for gripping, pulling and twisting.
- Holes in jaw for looping wire.
- Hardened to HRC45.
- Rust resistant black oxide finish.

Application

- Cut and Strip 10-20 AWG solid and 12-22 AWG stranded.
- Cut and chase threads on 16/32 & 8/32 bolts.
- Serrated plier nose for gripping, pulling and twisting.
- Holes in jaw for looping wire.

Part Numbers

15003C

ProStrip 10/20 Wire Strippers



Tips

How you use your tools is just as important as what tool you choose for an application.

Combing Your Braid

Coax stripping EZ!

Listen To Your Stripper

Your Coax stripper!

'POP' Your Cable Jacket

No more knicks.

FREE TOOL, Twisted Pair Separator

Who says nothing's free?

Cut Strip Terminate Test

Copyright © 2018 Platinum Tools®. All rights reserved.