



10" Euro Crimp Tool

P/N multiple

The 10" Euro Crimp Tool represents the next generation of crimp tool technology! It incorporates many innovative features delivering superior performance and value. The patented double cam ratchet mechanism delivers higher crimp force while reducing handle grip distance. Longer, high leverage handles produce more crimp force with less hand force. Extremely smooth ratchet design with no break over hand force. Straight plate lower jaw assembly design eliminates structural stress point, which is common in competitive tools. Easy to reach safety ratchet release. Quick Change Die Screws available - PN 17099



- Crimps insulated terminals to 10 AWG and non-insulated terminals to 8 AWG.
- Variety of crimp dies available for CATV F, BNC, TNC, SMB, SMA and N series coaxial connectors.
- Accepts crimp die sets from most other popular tools. Your old dies will work!

Part Numbers

17000C

10" Euro Crimp Tool, Frame Only

17001C

10" Euro Crimp Tool, for Insulated terminals 10 thru 22 AWG solid or stranded wire

17002C

10" Euro Crimp Tool, for non-insulated terminals 8 thru 22 AWG solid or stranded wire

17003C

10" Euro Crimp Tool, for coax BNC/TNC/HDTV RG59/6 & Belden 8281/1694A

17004C

10" Euro Crimp Tool, for coax BNC/TNC 3 Piece RG58/59/62AU

17005C

10" Euro Crimp Tool, for Coax CATV F Type 1 & 2 Piece RG59 & RG6

17006C

10" Euro Crimp Tool, for coax BNC/TNC & F, RG6/RG6Quad/8281

17007C

10" Euro Crimp Tool, for Euro Crimp Tool, for commercial insulated terminals

17008C

10" Euro Crimp Tool, for commercial open barrel

17009C

10" Euro Crimp Tool, for SMA/SMB/Mini 59/BNC/TNC/Mini UHF

17010C

10" Euro Crimp Tool, for N type plugs

17011C

10" Euro Crimp Tool, for HDTV/True 75 Ohm BNC/TNC

17099C

Quick Change Die Screws - Set of 2

Cut Strip Terminate Test

Copyright © 2018 Platinum Tools®. All rights reserved.