

**KEMET Part Number: PMR205AC6470M470R30**  
(P405CJ474M125AH471)

PMR205/P405, Film, Metallized Paper, Resistor/Capacitor, 0.47 uF, 20%, 250 VDC, 85C, Lead Spacing = 20.3mm



General Information	
Supplier:	KEMET
Series:	PMR205/P405
Dielectric:	Metallized Paper
Style:	Radial
Features:	RC Unit not approved
RoHS:	Yes
Lead:	Wire Leads
Construction:	Molded
Miscellaneous:	Resistor Tolerance: +/-30%. Resistor= 470 Ohms

Dimensions	
L	24mm MAX
H	15mm MAX
T	9mm MAX
S	20.3mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	0.47 uF
Capacitance Tolerance:	20%
Voltage AC:	125 VAC
Voltage DC:	250 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Insulation Resistance:	2.128 GOhms
Safety Class:	X2

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	200