

## HDC enclosures HDC IP68 06B TSS 1M25

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The new RockStar® enclosures are resistant to seawater and offer a high degree of shock resistance, meet IP 68 and IP 69K, and have been developed for use under extreme environmental conditions and designed for the high vibration requirements acc. to DIN EN 61373 cat. 2 (bogie). As such, this housing family is ideally suited for fault- and maintenance-free operation of heavy-duty connectors in transport and traffic engineering as well as in power engineering and in applications with extreme requirements. During development, measures were also implemented to make the enclosures extremely EMC-resistant.

### General ordering data

Type	HDC IP68 06B TSS 1M25
Order No.	<a href="#">1082530000</a>
Version	HDC enclosures, Size: 3, Protection degree: IP68, IP69K, Plug housing, Screw plug, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248845538
Qty.	1 pc(s).

**HDC enclosures  
HDC IP68 06B TSS 1M25**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	132 mm	Length (inches)	5.197 inch
Width	58 mm	Width (inches)	2.283 inch
Height	100.5 mm	Height (inches)	3.957 inch
Net weight	451 g		

**Temperatures**

Limit temperature	-50 °C ... 125 °C
-------------------	-------------------

**Dimensions**

Cable entry	w. threading	Total length housing	132 mm
-------------	--------------	----------------------	--------

**General data**

EMC housings	Yes	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP68, IP69K
Surface finish	Powder coating	Tightening torque	6.5 Nm

**Version**

Cable entry	w. threading	Clamp version	Screw plug
Design	Standard	Design of housing	Plug housing
Design of locking system	Screw plug	Internal thread	M 25
Number of cable entry on top	0	Number of cable entry sideways	1
Size	3	Size of cable entries	M 25
Suitable for ModuPlug®	Yes	Tightening torque	6.5 Nm
Top part/bottom part/lid	upper part	Type	Plug

**Classifications**

ETIM 3.0	EC000437	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC000437
UNSPSC	30-21-18-01	eClass 5.1	27-14-34-19
eClass 6.2	27-14-34-19	eClass 7.1	27-44-05-15
eClass 8.1	27-44-05-15	eClass 9.0	27-44-05-15
eClass 9.1	27-44-02-02		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN</a>

Creation date July 2, 2018 10:51:55 AM CEST

Catalogue status 29.06.2018 / We reserve the right to make technical changes.

**Data sheet**

**HDC enclosures  
HDC IP68 06B TSS 1M25**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

