

## Plugs

### KST 14/4



Product	KST 14/4
description	Jumper plug with spring-loaded 4 mm plugs and shatter-proof insulation, not stackable.
article-no. / *colour	9722671xx  ● 00 black  <span style="border: 1px solid black; padding: 2px;">Ni</span>
technical data	
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	32 A
material plug	brass, nickel plated
housing material	PBT
temperature range acc. To IEC61010 <sup>(2)</sup>	-15 °C to 70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
standard	IEC 61010

<sup>(1)</sup> for normal environmental conditions -5°C to +40°C

<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(3)</sup> Other circuits that are not directly connected to mains

stand: 26.07.2018