


KEMET, EFA, Flex Suppressors, Commercial Grade



General Information	
<b>Series:</b>	EFA
<b>Style:</b>	Sheet
<b>Description:</b>	Flex Suppressor Flame Retardant Type
<b>Features:</b>	Flame Retardant Type
<b>RoHS:</b>	Yes
<b>Qualifications:</b>	UL94 V-0, UL File No. E176124
<b>Environment:</b>	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions	
<b>Sheet Size</b>	240x30mm
<b>L</b>	240mm NOM
<b>W</b>	30mm NOM
<b>T</b>	0.2mm NOM

Specifications	
<b>Temperature Range:</b>	-40/+105C
<b>Magnetic Permeability:</b>	60 TYP At 3MHz
<b>Effective Frequency:</b>	10 GHz MAX
<b>Resistance:</b>	1 MOhms MIN
<b>Specific Gravity:</b>	3.1 Atm TYP
<b>Conductivity:</b>	1.3 W/m K
<b>Tensile Strength:</b>	6.8 MPa

Packaging Specifications	
<b>Tape Description:</b>	No Adhesive Tape
<b>Weight:</b>	4.464 kg