

KEMET, EFA, Flex Suppressors, Commercial Grade



General Information	
Series:	EFA
Style:	Sheet
Description:	Flex Suppressor Flame Retardant Type
Features:	Flame Retardant Type
RoHS:	Yes
Qualifications:	UL94 V-0, UL File No. E176124
Environment:	RoHS Compliant, Halogen Free, PVC Free, Lead Free, Red Phosphorus Free

Dimensions	
Sheet Size	240x50mm
L	240mm NOM
W	50mm NOM
T	0.1mm NOM

Specifications	
Temperature Range:	-40/+105C
Magnetic Permeability:	60 TYP At 3MHz
Effective Frequency:	10 GHz MAX
Resistance:	1 MOhms MIN
Specific Gravity:	3.1 Atm TYP
Conductivity:	1.3 W/m K
Tensile Strength:	6.8 MPa

Packaging Specifications	
Tape Description:	Without PET Tape (Txx00)
Tape Thickness:	0.03mm
Weight:	3.9024 kg