

Share:



## RBC47



Description: Genuine APC RBC(TM) are tested and certified for compatibility to restore UPS performance to the original specifications.

Includes : All required connectors , Battery recycling guide , Installation Guide , Reusable packaging

## Product Support

- User Manual
- Product Registration
- Product FAQs

Product Overview

Technical Specifications

Documentation

### Output

Print Technical Specification

Battery Capacity (mAh)	3200
Battery Output Voltage	12.0

### Input

Number of Power Cords	1
-----------------------	---

### Batteries & Runtime

Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	3 - 5
RBC Quantity	1

### Physical

Maximum Height	66mm , 6.6CM
Maximum Width	67mm , 6.7CM
Maximum Depth	134mm , 13.4CM
Net Weight	1.4KG
Shipping weight	1.67KG
Shipping Height	94mm , 9.4CM
Shipping Width	146mm , 14.6CM
Shipping Depth	187mm , 18.7CM
Color	Black

### Environmental

Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-1500meters

## Conformance

---

Standard warranty 30 days (Japan only)

## Sustainable Offer Status

---

PEP Available in Documentation tab

EOLI Available in Documentation tab