



ART.-NR. 114.04 | P

run

Ein echter Selbstläufer – bequem im Handling, extrem im Fassungsvermögen.

- mobiler Koffer mit anwendungsfreundlichem Teleskopgriff und 2 Inline-Rollen
 - Kofferschalen aus hochschlagzähem ABS-Material
 - robuster Aluminiumrahmen mit Stoßkantenschutz
 - 2 abschließbare Kippschlösser sowie 1 B&W PROFIcone-Zahlschloss
 - B&W CONVENIENCE-Griff
 - Scharnierabdeckung und Sicherheitsdeckelhalter
 - Dokumentenfach im A4-Format
 - Bodenschale variabel
 - In 3 Innenausstattungen lieferbar
-
- mobile case with user-friendly telescopic handle and two free running rollers
 - case shells made of dentproof ABS material
 - robust aluminium frame with protection for the sharp edges
 - two lockable cliplocks plus one B&W PROFIcone combination lock
 - B&W CONVENIENCE handle
 - comfortable lid holder and hinge cover
 - document partition in the lid (A4 format)
 - variable floor shell
 - available in three interior trims

run pockets

- herausnehmbare Werkzeugtafel im Deckel mit 22 Tool Pockets auf Vorder- und Rückseite
 - herausnehmbare Abdeckplatte für Bodenschale mit 15 Tool Pockets
-
- removable tool board in the lid with 22 tool pockets in the front and back
 - removable cover board for the floor shell with 15 tool pockets

INNENMAßE

INTERIOR MEASUREMENTS

485 X 350 X 195 MM
19 X 13,75 X 7,75 INCH

AUSSENMAßE

EXTERIOR MEASUREMENTS

500 X 430 X 270 MM
19,75 X 17 X 10,75 INCH

GEWICHT / WEIGHT

8,0 KG / 16 POUNDS

VOLUMEN / VOLUME

36,0 L

MAX. ZULADUNG

MAX. LOADING CAPACITY

30 KG / 66 POUNDS

ART.-NR. 114.04

114.04 / P = POCKETS

114.04 / L = LOOPS

114.04 / M = MODUL