

Full Metal Hoods

DTZF-RG+D-Sub Solder Cup

TECHNICAL SPECIFICATIONS

D-Sub Hood:

Material: Zinc, Nickel Plated
 Operating Temperature: -45°C to + 105°C
 Cable Entry: Top Entry
 Thumbscrews: UNC 4-40 (Standard)


Cable O.D - Standard:
 9-Way: Up to 6,5mm with grommet - 9,5mm without grommet
 15-Way: Up to 6,5mm with grommet - 12,5mm without grommet
 25-Way: Up to 8,0mm with grommet - 12,5mm without grommet
 37-Way: Up to 9,0mm with grommet - 15,0mm without grommet

Standard D-Sub Solder Cup:

Insulator: Glass filled TP, UL94 V-0
 Shell: Steel, Tin Plated
 Contact pins: Copper Alloy
 Gold Flash over Ni.
 Stamped & Formed Pins: Class 3, 100 inserts min.
 Contact Plating: Gold flash over Nickel
 Operating Temperature: -55°C to +85°C
 Withstanding voltage: >1000V Rms to 50 Hz
 for 1 minute
 Current Rating: 5A
 Insulator resistance: >5000MΩ min.

Features:

- Available in sizes 9-15-25-37
- Excellent EMI Shielding
- Re-openable
- Spring-Clip mounted Jackscrews



Size DTZF	Dim A	Dim B	Dim C
9-way	31,6	39,5	15,2
15-way	40,0	41,0	15,2
25-way	53,7	47,5	15,2
37-way	70,2	48,0	15,2

Ordering information:

Standard D-Sub Connector Kits

Size:	P/N - Kitted:	Description:
9-way	L17DTZF09-RG+L717SDE09P	Solder Cup, 9-Male
15-way	L17DTZF15-RG+L717SDA15P	Solder Cup, 15-Male
25-way	L17DTZF25-RG+L717SDB25P	Solder Cup, 25-Male
37-way	L17DTZF37-RG+L717SDC37P	Solder Cup, 37-Male

Size:	P/N - Kitted:	Description:
9-way	L17DTZF09-RG+L77SDE09S	Solder Cup, 9-Female
15-way	L17DTZF15-RG+L77SDA15S	Solder Cup, 15-Female
25-way	L17DTZF25-RG+L77SDB25S	Solder Cup, 25-Female
37-way	L17DTZF37-RG+L77SDC37S	Solder Cup, 37-Female