

# Straight BNC Plug, Crimp



## Specifications

Connector Body Style : Straight Plug  
 Coaxial Termination : Crimp  
 Connector Mounting : Cable  
 Coaxial Cable Types : Belden 1649A

## Electrical Specifications

Frequency Range : DC-6GHz  
 Nominal Impedance : 75Ω  
 Voltage Rating : 300V Max.  
 VSWR : 1.3 Max.

## Material Specifications

Bodies : Brass per JIS-C3604  
 Centre Contact : Brass per JIS-C3604  
 Insulation : PTFE per ASTM D1457 and ASTM D1710  
 Crimp Ferrule : Brass per JIS-C2700


## Mechanical Specifications

Interface in accordance with : MIL-STD-348B  
 Cable Attachment : Outer: Crimp / Inner: Solder  
 Crimp Size Required : Ferrule: 7.1mm (0.28") HEX. Crimp Tool

## Environmental Specification

Operating Temperature : -65°C to +165°C

## Diagram



Dimensions : Millimetres (Inches)

No.	Description	Material	Finish/Colour
1	Body	Brass	Nickel 100µ" Min.
2	Washer	Brass	Nickel
3	Spring Washer	SK-5	Nickel
4	Washer	Brass	Nickel
5	Gasket	Silicone	Red

No.	Description	Material	Finish/Colour
6	Insulation	PTFE	-
7	Shell	Brass	Nickel 100µ" Min.
8	Crimp Ferrule	Brass	Nickel
9	Centre Contact	Brass	Gold 3µ" Min.

# Straight BNC Plug, Crimp



## Part Number Table

Description	Part Number
Straight BNC Plug, Crimp, 75Ω, Belden 1649A	MC002947

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell Limited 2016.

[www.element14.com](http://www.element14.com)  
[www.farnell.com](http://www.farnell.com)  
[www.newark.com](http://www.newark.com)

