

Han M23 P HBM Front M25x1,5



Part number	09 15 600 0313
Specification	Han M23 P HBM Front M25x1,5
HARTING eCatalogue	https://b2b.harting.com/09156000313

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M23 Power
Type of hood/housing	Bulkhead mounted housings
Description of hood/ housing	Straight Front mounting

Version

Size	M23
Fixing	Thread M25 x 1.5

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 / IP69 / IPX9K acc. to ISO 20653 in locked position

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	5
Net weight	34.8 g
Country of origin	Germany
Customs tariff number	85366990