

7432 Krafftform adjustable torque screwdrivers with Rapidaptor quick-release chuck, 1/4 inch, 0,90 - 1,50 Nm
Series 7400 Krafftform Torque Screwdrivers



EAN:	4013288179135	Size:	155x37x37 mm
Part number:	05074774001	Weight:	122 g
Article number:	7400	Country of origin:	CZ
		Customs tariff number:	82054000



- Adjustable Krafftform torque screwdriver with Rapidaptor quick-release chuck
- Suitable for bits with 1/4" hex head drive
- Rapidaptor technology for rapid bit change
- Distinct signal when pre-set value is reached
- Numerical torque value indicator

Wera torque screwdriver. Variable torque setting option with highest precision. Simple adjustment of the required torque value without any special tools. Easy-to-read scale value; audible click signal. Rapidaptor quick-release technology for rapid bit change. Unlimited torque to loosen seized screws. Multi-component Krafftform handle with hard and soft zones for high working speeds, whilst being easy on the hand. Suitable for bits with 1/4" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3 (ISO 1173).

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_series_7400_krafftform_torque_screwdrivers_7400.html

Wera - 7400
05074774001 - 4013288179135

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

Adjustable Torque Screwdrivers

Simple setting

Easy-to-read



Many screws – particularly in assembly and maintenance applications – have to be tightened with controlled torque to ensure the dependability of the screw connection and/or to avoid damage to the screw or work piece. Wera’s adjustable torque screwdrivers are the ideal tool for this. They feature a torque range of 0.3 Nm to 8.8 Nm, two different handles, measurement accuracy of $\pm 6\%$ and Rapidaptor technology for rapid bit change.

Wera’s adjustable torque screwdrivers allow variable torque settings with maximum precision and ensure that the user gets the very best results in the familiar Wera design with superior ergonomics.

Simple setting of the required torque by hand.

Easy-to-read scale value.

Attachable magnifying glass

Measurement accuracy

Unlimited torque

Versatile



Articles 7430, 7431 and 7432 all come with a magnifying glass. This can be easily attached on to the scale, dramatically improving visibility.

Measurement accuracy is $\pm 6\%$ in accordance with the standard DIN EN ISO 6789. Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Unlimited torque for loosening seized screws.

Rapidaptor technology makes the tool adaptable since bits and sockets can be exchanged rapidly.

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_series_7400_krafftform_torque_screwdrivers_7400.html







Wera - 7400
05074774001 - 4013288179135

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

7432 Krafftform adjustable torque screwdrivers with Rapidaptor quick-release
 chuck, 1/4 inch, 0,90 - 1,50 Nm
 Series 7400 Krafftform Torque Screwdrivers



Further versions in this product family:

								
	art. no.	mm	inch	nm	nm	mm	inch	
	05074770001 ¹⁾	7430	89	1/4	0.10-0.34	0.015	142	5 7/16
	05074772001 ¹⁾	7431	89	1/4	0.30-1.00	0.05	142	5 7/16
	05074774001¹⁾	7432	89	1/4	0.90-1.50	0.05	142	5 7/16
	05074700001	7440	105	1/4	0.3-1.2	0.05	155	6
	05074701001	7441	105	1/4	1.2-3.0	0.10	155	6

1) With attachable magnifying glass, dramatically improving visibility.

Web link

http://products.wera.de/en/tools_for_the_aerospace_segment_series_7400_krafftform_torque_screwdrivers_7400.html

Wera - 7400
 05074774001 - 4013288179135

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de