



3W
 VT-523 3W EMERGENCY EXIT LIGHT COLORCODE:6000K

Lumens 140	Dimensions 350x117x60mm
-----------------------------	--

White
 SKU:8096



Technical Information

Instant Start:	0-100% in 11s	Body Type:	PC
Watts:	3	Long life:	20,000 Hours
Lumens:	140	LED Chip Type:	SMD
Battery Charging Current:	70-150mA	IP Rating:	IP65
Battery Discharging Current:	100-450mA	Dimmable:	No
No. Of Led:	16	Warranty (Years):	2
Battery Type:	Ni-Cd 4.8V,1500mAh	Operation Temperature:	-20 to +45°C
Charging Time:	24 Hours	Input Power:	AC:220-240V,50/60Hz
Emergency Operation Time:	>3 Hours		

Features

- ✓ Efficient thermal management technology.
- ✓ High performance Ni-Cd batteries made for Longevity & low maintenance.
- ✓ LEDs mounted on print circuit board.
- ✓ Low energy consumption only 20 watts at 120V.
- ✓ Thermoplastic PC housing, Rectangular type plastic with different signs.
- ✓ Single or double face configuration.
- ✓ Reliable Emergency backup of 3 hours.
- ✓ Universal (wall, side or ceiling) mounting.

2 YEAR WARRANTY

CE/EMC

