

Han M23 P 5+PE Male -C



Part number	09 15 606 3001
Specification	Han M23 P 5+PE Male -C
HARTING eCatalogue	https://b2b.harting.com/09156063001

Identification

Category	Inserts
Series	Han [®] M23 Power
Element	Inserts

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	5
PE contact	Yes
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 4 mm ²
Electrical data acc. to IEC 61984	28 A 600 V 4 kV 3
Rated current	28 A
Rated voltage	600 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹³ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500
Test voltage U _{r,m.s.}	4 kV

Material properties

Material (insert)	Polyamide
Colour (insert)	Blue
Flammability acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance

Material properties

China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	5
Net weight	5.92 g
Country of origin	Germany
Customs tariff number	85366990