

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1062835003](#)
Status: **Active**
Overview: [QSFP+ Interconnect Solution](#)
Description: Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8 LC Multimode 50/125µm 3mm Round Cable Plenum, Standard Bandwidth(OM2), 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------------|---|
| Product Family | Fiber Optic Assemblies |
| Series | 106283 |
| Boot Type | N/A |
| Connector to Connector | MTP-to-LC |
| Mode | Multimode Enhanced |
| Overview | QSFP+ Interconnect Solution |
| Product Name | iPass+ HD, MPO, QSFP Plus, QSFP+ |
| UPC | 822350976763 |

Physical

| | |
|-----------------------|----------|
| Cable Length | 5.0m |
| Cable Size | 3.00mm |
| Fiber (Core/Cladding) | 50/125µm |
| Net Weight | 82.234/g |
| Single Ended | No |
| Wire/Cable Type | Round |

Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------|--------------------|
| Sales Drawing | SD-106283-5XXX-001 |
|---------------|--------------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018) 2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Relevant

Search Parts in this Series

[106283 Series](#)