

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1062835301](#)

Status: **Active**

Overview: [QSFP+ Interconnect Solution](#)

Description: Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8LC Multimode 50/125µm 3mm Round Cable Plenum, High Bandwidth (OM3), 1.0m (3.28') Length, Aqua Cable

Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Fiber Optic Assemblies
Series	106283
Boot Type	N/A
Connector to Connector	MTP-to-LC
Mode	Multimode Enhanced
Overview	QSFP+ Interconnect Solution
Product Name	iPass+ HD, MPO, QSFP Plus, QSFP+
UPC	800756706450

Physical

Cable Length	1.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	47.300/g
Single Ended	No
Wire/Cable Type	Round

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-106283-5YYY
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[106283 Series](#)