

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190700038**
Status: **Active**
Overview: Solderless Terminals
Description: InsulKrimp Ring Tongue Terminal for 18-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-009-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19070
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview Solderless Terminals
 Product Name InsulKrimp
 Type Ring
 UPC 800753069008

Physical


Barrel Type Closed
 Flammability 94V-0
 Insulation PVC
 Material - Plating Mating Tin
 Net Weight 0.583/g
 Packaging Type Bag
 Stud Size 3-4 (M2.6)
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 3.70mm max.
 Wire Size AWG 18, 20, 22
 Wire Size mm² 0.35-0.80

Material Info

Engineering Number AA-232-04X

Reference - Drawing Numbers

Product Specification PS-19902-009-001, PS-19902-011-001,
 PS-19902-013-001
 Sales Drawing SD-19070-003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/01/2018 (15
 January 2018)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19070 Series](#)