

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640043](#)
Status: **Active**
Overview: [Splices](#)
Description: Perma-Seal Step Down Butt Splice for 14-16 AWG to 18-22 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Splices](#)
Series [19164](#)
Comments [Step down: 14/16 to 18/22 AWG](#)
Crimp Quality Equipment [Yes](#)
Mil-Spec [N/A](#)
Overview [Splices](#)
Product Name [Butt - Step Down, Perma-Seal](#)
UPC [800753113282](#)

Physical

Barrel Type [Closed](#)
Color - Resin [Blue](#)
Insulation [NiAc](#)
Material - Metal [Copper](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [2.916/g](#)
Packaging Type [Bag](#)
Temperature Range - Operating [-55° to +125°C](#)
Wire Insulation Diameter [5.84mm max.](#)
Wire Size AWG [14, 16, 18, 20, 22](#)

Electrical

Voltage - Maximum [600V](#)

Material Info

Engineering Number [SBA-631](#)

Reference - Drawing Numbers

Product Specification [PS-19902-011-001, PS-19902-013-001](#)
Sales Drawing [SD-19164-029](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19164 Series](#)