

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640057](#)
Status: **Active**
Overview: [Splices](#)
Description: Perma-Seal Butt Splice for 10-12 AWG Wire, Mylar Tape Carrier

Documents:

[3D Model](#) [Product Specification PS-19902-015-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family [Splices](#)
 Series [19164](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Splices](#)
 Product Name Butt - Funnel Entry, Perma-Seal
 UPC 800753113428

Physical

Barrel Type Closed
 Color - Resin Yellow
 Insulation NiAc
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 3.422/g
 Packaging Type Adhesive Tape on Reel
 Temperature Range - Operating -55° to +125°C
 Wire Insulation Diameter 7.87mm max.
 Wire Size AWG 10, 12

Electrical


Voltage - Maximum 600V

Material Info

Engineering Number SC-12-10T

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-015-001
 Sales Drawing SD-19164-017



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19164 Series](#)