

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192030099](#)
Status: **Active**
Overview: [High-Temperature Temp Terms Terminals and Splices](#)
Description: VersaKrimp Temp-Term Ring Tongue Terminal for 10 to 12 AWG Wire, Stud Size 10 (M5)

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19203](#)
 Comments 650° F (343° C)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [High-Temperature Temp Terms Terminals and Splices](#)
 Product Name Temp-Terms, VersaKrimp
 Type Ring
 UPC 800755059519

Physical

Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Nickel
 Net Weight 1.480/g
 Packaging Type Bag
 Stud Size 10 (M5)
 Wire Size AWG 10, 12
 Wire Size mm² 4.00-6.00

Material Info

Engineering Number C-T-328-10

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing CTCD30101



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19203 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION