

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192040029](#)
Status: **Active**
Overview: [Splices](#)
Description: Avikrimp 4 Way Splice for 10-12 AWG Wire

Documents:

Drawing (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification PS-19902-009-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)	

General

Product Family	Splices
Series	19204
Comments	4 Way Connector
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Splices
Product Name	4 Way, Avikrimp
UPC	800753051850

Physical

Barrel Type	Closed
Color - Resin	Natural
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	9.404/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	5.72mm max.
Wire Size AWG	10, 12
Wire Size mm ²	3.30-5.00

Electrical


Voltage - Maximum	600V
-------------------	------

Material Info

Engineering Number	C-5XC
--------------------	-------

Reference - Drawing Numbers

Product Specification	PS-19902-009-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19204-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19204 Series](#)