

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0192150037](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Step Down Butt Splice for 8-12 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family [Splices](#)  
 Series [19215](#)  
 Comments Step down: 8 to 10/12 AWG  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 Overview [Splices](#)  
 Product Name Butt - Step Down  
 UPC 800755062571

**Physical**

Barrel Type Closed  
 Insulation None  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 4.705/g  
 Packaging Type Bag  
 Temperature Range - Operating 149°C  
 Wire Insulation Diameter N/A  
 Wire Size AWG 10, 2, 8  
 Wire Size mm<sup>2</sup> N/A

**Material Info**

Engineering Number DC-354

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19215-004



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/61/2018 (27 June  
 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19215 Series](#)