

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002068103](#)
Status: **Active**
Overview: Standard .062" Pin and Socket Power Connectors
Description: 1.57mm Diameter, Standard .062" Pin and Socket PC Tail Terminal, Series 1778, Male, with Tin (Sn) Plated Brass Contact, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-1190-003 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	1778
Application	Power, Wire-to-Wire
Comments	PC Tail Brass for Standard .062" Housing
Crimp Quality Equipment	Yes
Overview	Standard .062" Pin and Socket Power Connectors
Product Name	Standard .062"
UPC	800753693128

Physical


Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.156/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Through Hole
Wire Insulation Diameter	3.00mm max.
Wire Size AWG	N/A
Wire Size mm ²	N/A

Material Info

Engineering Number	1778-(P909)L
--------------------	--------------

Reference - Drawing Numbers

Packaging Specification	PK-1190-003
Sales Drawing	SD-1778-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1778 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Manual Extraction

[0011030002](#)

Tool