

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0357450410](#)
Status: **Active**
Overview: [VersaBlade Wire-to-Wire Connector System](#)
Description: [VersaBlade .070 Male Crimp Terminal, 24 AWG, Type A](#)

Documents:

3D Model	Product Specification 351800600-001 (PDF)
Drawing (PDF)	Packaging Specification PK-35745-001-001 (PDF)
Product Specification 351800400-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	35745
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	756054339091

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.253/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.20mm max.
Wire Size AWG	24
Wire Size mm ²	N/A


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-35745-002-001
Packaging Specification	PK-35745-001-001
Product Specification	351800400-001, 351800600-001
Sales Drawing	SD-35745-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[35745](#) Series

Mates With

[35746](#) Crimp Terminal

Use With

[35150](#) VersaBlade Hybrid Receptacle
Housing. [35151](#) VersaBlade Hybrid Plug
Housing