

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0510670600](#)  
**Status:** **Active**  
**Description:** 3.50mm Pitch Wire-to-Wire and Wire-to-Board Housing, Positive Lock, 6 Circuits, Natural

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51067-016 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51067-017 (PDF)</a>
<a href="#">Product Specification PS-51067-002-001 (PDF)</a>	<a href="#">Product Specification PS-51067-018 (PDF)</a>
<a href="#">Product Specification PS-51067-003 (PDF)</a>	<a href="#">Product Specification PS-51067-019-001 (PDF)</a>
<a href="#">Product Specification PS-51067-004 (PDF)</a>	<a href="#">Product Specification PS-51067-020-001 (PDF)</a>
<a href="#">Product Specification PS-51067-005 (PDF)</a>	<a href="#">Product Specification PS-51067-021-001 (PDF)</a>
<a href="#">Product Specification PS-51067-006 (PDF)</a>	<a href="#">Product Specification PS-51067-022-001 (PDF)</a>
<a href="#">Product Specification PS-51067-007 (PDF)</a>	<a href="#">Product Specification PS-51067-023-001 (PDF)</a>
<a href="#">Product Specification PS-51067-008 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">51067</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	N/A
UPC	800753630611


**Physical**

Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	1247.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-51067-002-001, PS-51067-003, PS-51067-004, PS-51067-005, PS-51067-006, PS-51067-007, PS-51067-008, PS-51067-016, PS-51067-017, PS-51067-018, PS-51067-019-001, PS-51067-020-001, PS-51067-021-001, PS-51067-022-001, PS-51067-023-001
Sales Drawing	SD-51067-**00



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[51067 Series](#)

**Mates With**

[51114](#) , [53258](#) , [53259](#) , [53265](#) , [53266](#)

**Use With**

[50217 Crimp Terminals](#)