

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0511420200](#)
Status: **Active**
Description: 6.50mm Pitch Wire-to-Board Receptacle Housing, 2 Circuits, Natural

Documents:

[3D Model](#) [Product Specification PS-51142-003 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51142-002-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series [51142](#)
 Application Power, Wire-to-Board
 Product Name N/A
 UPC 800753323575


Physical

Circuits (maximum) 2
 Color - Resin Natural
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Material - Resin Polyester
 Net Weight 945.000/mg
 Number of Rows 2
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 6.50mm
 Stackable No
 Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers

Product Specification PS-51142-002-001, PS-51142-003
 Sales Drawing SD-51142-002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51142 Series](#)

Mates With

[53721](#) , [53728](#)

Use With

[50597](#) , [51143](#) , [50598](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION