

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638019200](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Bench Top Pneumatic Wire Stripper for 12-26 AWG

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

General

Product Family	Application Tooling
Series	207122
Comments	See Tooling Specification (PDF) Above
Function	Wire Stripping
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Literature Order No	987650-5031
Product Name	N/A
Tool Type	Pneumatic Wire Stripper
UPC	884982191051
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Engineering Number WS-1000

Reference - Drawing Numbers

Application Tooling Documents
 TM-638019200, TM-638019200CN, TM-638019200DE,
 TM-638019200FR, TM-638019200IT,
 TM-638019200JP, TM-638019200KR,
 TM-638019200MY, TM-638019200PL,
 TM-638019200RU, TM-638019200SK,
 TM-638019200SP, TM-638019200TH,
 TM-638019200TW, TM-638019200VN



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/30/2017 (7 July
 2017)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[207122](#) Series