

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0733910080](#)  
**Status:** **Active**  
**Overview:** [SMA RF Connectors](#)  
**Description:** 50 Ohms, SMA Right-Angle PCB Jack, Nickel (Ni) Plated, 80 Pieces Per Tray

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family [RF/Coax Connectors](#)  
 Series [73391](#)  
 Overview [SMA RF Connectors](#)  
 Product Name [SMA](#)  
 Style [PCB](#)  
 Type [Subminiature](#)  
 UPC [756054714959](#)  
 Wire/Cable Type [N/A](#)

**Physical**

Gender [Jack](#)  
 Keying to Mating Part [None](#)  
 Net Weight [2.952/g](#)  
 Orientation [Right Angle](#)  
 PCB Mounting [Through Hole](#)  
 Packaging Type [Tray](#)  
 Panel Mount [No](#)  
 Panel Mount Method [N/A](#)

**Electrical**

Frequency [18 GHz](#)  
 Impedance [50Ω](#)

**Solder Process Data**

Duration at Max. Process Temperature (seconds) [010](#)  
 Lead-freeProcess Capability [SMC&WAVE](#)  
 Max. Cycles at Max. Process Temperature [002](#)  
 Process Temperature max. C [260](#)

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing [SD-73391-008](#)



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - ED/61/2018 (27 June 2018)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
Prop65	Duty-To-Declare
PropRisk	Cancer
PropRisk	Developmental toxicity
PropRisk	Reproductive toxicity
PropSub	Lead and its compounds
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[73391](#) Series

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**