

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747630010](#)
Status: **Active**
Overview: [QSFP+ Interconnect Solution](#)
Description: QSFP+ Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 0dB

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E107635

General

Product Family I/O Connectors
 Series [74763](#)
 Application Module-to-Board
 Component Type Adapter
 Overview [QSFP+ Interconnect Solution](#)
 Product Name QSFP
 Type N/A
 UPC 883906054281

Physical

Boot Color N/A
 Circuits (Loaded) N/A
 Color - Resin Blue (Light)
 Flammability 94V-0
 Gender Dual
 Lock to Mating Part No
 Material - Plating Mating Nickel
 Orientation Horizontal
 Packaging Type Tray
 Panel Mount No
 Pitch - Mating Interface N/A
 Polarized to Mating Part No
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact N/A
 Shielded No
 Voltage - Maximum 3.3V

Material Info



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[74763 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION