

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0747630025](#)  
**Status:** **Active**  
**Overview:** [QSFP+ Interconnect Solution](#)  
**Description:** QSFP+ Universal Loopback Adapter, 100 Ohms Impedance, Serial ID, 5dB, 12C Port Expander

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E107635

**General**

Product Family I/O Connectors  
 Series [74763](#)  
 Application Module-to-Board  
 Component Type Adapter  
 Overview [QSFP+ Interconnect Solution](#)  
 Product Name QSFP  
 Type N/A  
 UPC 800756931807

**Physical**

Boot Color N/A  
 Circuits (Loaded) N/A  
 Color - Resin Light Green  
 Flammability 94V-0  
 Gender Dual  
 Lock to Mating Part No  
 Material - Plating Mating Nickel  
 Net Weight 33.204/g  
 Orientation Horizontal  
 Packaging Type Tray  
 Panel Mount No  
 Pitch - Mating Interface N/A  
 Polarized to Mating Part No  
 Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact N/A  
 Shielded No  
 Voltage - Maximum 3.3V

**Material Info**



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Contained Per -  
 ED/01/2018 (15  
 January 2018)  
 2,4-Di-tert-butyl-6-(5-  
 chlorobenzotriazol-2-  
 yl)p

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[74763 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**