

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982670233](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 8 Circuits, 0.152m Cable Length, Tin(Sn) Plating

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-98267-001-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-98267-001-001 (PDF)	

General

Product Family	Cable
Series	98267
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Literature Order No	987650-6631
Product Name	Premo-Flex FFC Jumper
UPC	756054770634

Physical

Cable Length	0.152m
Circuits (Loaded)	8
Circuits (maximum)	8
Net Weight	0.911/g
Packaging Type	Bag
Pitch - Termination Interface	1.00mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98267-001-001
Product Specification	PS-98267-001-001
Sales Drawing	SD-98267-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[98267](#) Series

Use With

[52207](#) , [52271](#) , [52852](#) , [52793](#) , [52808](#) , [52610](#) , [52807](#) , [52030](#) , [52806](#)
<http://www.molex.com/product/ffc>
Molex FFC – FPC connector. Be sure to match like plating.