

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0193240012](#)
Status: **Active**
Overview: Metric Ring Terminals
Description: Avikrimp Metric Ring Terminal for Stud Size 8 (M4), Insulated Barrel

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

UL E32244

General

Product Family Ring and Spade Terminals
 Series [19324](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [Metric Ring Terminals](#)
 Product Name Avikrimp
 Type Ring
 UPC 887191290126

Physical

Barrel Type Closed - Brazed
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper Alloy
 Material - Plating Mating Tin
 Net Weight 2.138/g
 Packaging Type Bag
 Stud Size M4
 Wire Size AWG N/A
 Wire Size mm² 2.50-6.00

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number C6-836-M4

Reference - Drawing Numbers

Sales Drawing SD-19324-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19324 Series](#)