

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0345660103](#)
Status: **Active**
Overview: [MX123 Sealed Connection System](#)
Description: 2.54mm Pitch, MX123 Female Receptacle Housing, Keying Option A, Wire Dress Option 0, 73 Circuits, Black TPA

Documents:

3D Model	Product Specification TS-34566-1546-001 (PDF)
Drawing (PDF)	Application Specification AS-34566-001-001 (PDF)
Product Specification PS-34566-0000-001 (PDF)	Packaging Specification PK-31300-019 (PDF)
Product Specification TS-34566-002-001 (PDF)	RoHS Certificate of Compliance (PDF)



Series image - Reference only

General

Product Family	Crimp Housings
Series	34566
Application	Power, Wire-to-Board
Comments	See Sales Drawing for number of Open Circuits
Overview	MX123 Sealed Connection System
Product Name	MX123
UPC	822348356751

Physical

Circuits (maximum)	73
Circuits Detail	73
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	50.423/g
Number of Rows	4
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	11.0A, 25.0A
-------------------------------	--------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34566-001-001
Packaging Specification	PK-31300-019
Product Specification	PS-34566-0000-001, TS-34566-002-001, TS-34566-1546-001
Sales Drawing	12642695-001, 345660001-SD-000, SD-34566-001-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[34566 Series](#)

Mates With

MX123 Header [31386](#) , [31387](#)

Use With

MX64 Female Terminals [33467](#) (AWG, Gold)
MX64 Female Terminals [34736](#) (AWG, Silver)
MX64 Female Terminals [34736](#) (ISO, Silver)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION