

EREM

Part Number: 544D

Description: Chain nose pliers with inside-serrated jaws for secure handling



Pliers for miniature and standard electronics  
Non-reflecting surface, ESD-safe, high grade tool steel

Technical Data:

Length mm	120
Jaw length in mm	23
Head width mm	9
Head thickness mm	6.5
Width of tips in mm	1
Total height of both tips in mm	1.4
Material	Special tool steel
Weight in g	67
Length inches	4.724
Weight in oz	2.64
Jaw length inches	0.91

Head thickness inches	0.26
Head width inches	0.35
Head length inches	0.039
Head length mm	1
Total height of both tips in inches	0.055
Width of tips in inches	0.039
ESD-safe	on