

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151370603](#)
Status: **Active**
Overview: [Mini-Lock Wire-to-Board Connector System](#)
Description: Mini-Lock-to-Mini-Lock Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Female-Female, Single Row, 300.00mm Length, 6 Circuits, Natural

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	15137
Application	Signal, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mini-Lock-to-Mini-Lock
Overmolded	No
Overview	Mini-Lock Wire-to-Board Connector System
Product Name	Mini-Lock
UPC	191128925518

Physical

Cable Length	300.00mm
Circuits (Loaded)	6
Color - Resin	Natural
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Polyester
Net Weight	11.990/g
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	0.889µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	22
Wire/Cable Type	UL 1061


Electrical

Voltage - Maximum	250V AC (RMS)/DC
-------------------	------------------

Material Info

Reference - Drawing Numbers

Sales Drawing	151370600-000
---------------	---------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15137 Series](#)

Mates With

[53375](#) , [53426](#)