

**Order symbol:** ARK865CHTSSF  
**Product nbr:** 8561443  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque cover w/S.S. Lockable twist latch. Base includes 1/2 and 3/4 inch knock-outs and plastic flange mounts.

**EAN:** 6418074096197  
**EI. number:**  
**Finland:**

Including: Hinged cover. Base with 10-32 brass inserts, latched cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:		
	Length	Width	Height		
mm:	203	152	127	ALBP86	Aluminum Back Panel
inch:	8.0	6.0	5.0	ADFP86	Dead Front Panel w/ screws
<b>Materials:</b>			ASP86	Aluminum Swing Panel	
<b>Material:</b>	Polycarbonate		ASPK86	Swing Panel Kit incl. Panel	
<b>Base colour:</b>	RAL 7035 -light grey		ASPHK8	Swing Panel Kit w/o Panel	
<b>Cover screws material:</b>	Stainless steel		AMFL6	6" Mounting Flange Set	
<b>Cover colour:</b>	RAL 7035 -light grey		<b>Rating:</b>		
<b>Gasket material:</b>	Polyurethane		Ingress Protection (EN 60529): IP66/IP67		
<b>Temperatures:</b>			Impact Resistance (EN 62262): IK09		
<b>Temperature °C (short term):</b>	-40 ... 140 °C		Electrical insulation: Totally insulated		
<b>Temperature °C (continuous):</b>	-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
<b>Temperature °F (short term):</b>	-40 ... 284 °F		UV resistance: UL 508		
<b>Temperature °F (continuous):</b>	-40 ... 175 °F		Flammability Rating: UL 508		
<b>Accessories:</b>			Glow Wire Test (IEC 695-2-1) °C: 960		
ABP86	Painted Steel Back Panel		NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		

