

Order symbol: ARK1086SCF
Product nbr: 8561503
Description: PC Enclosure
Remarks: Opaque screw cover. Base includes 1/2 and 3/4 inch knock-outs and plastic flange mounts.

EAN: 6418074096791
EI. number:
Finland:

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	254	203	152	ALBP108 Aluminum Back Panel
inch:	10.0	8.0	6.0	ADFP108 Dead Front Panel w/ screws
Materials:			ASP108 Aluminum Swing Panel	
Material:	Polycarbonate		ASPK108 Swing Panel Kit incl. Panel	
Base colour:	RAL 7035 -light grey		ASPHK10 Swing Panel Kit w/o Panel	
Cover screws material:	Stainless steel		AMFL8 8" Mounting Flange Set	
Cover colour:	RAL 7035 -light grey		Rating:	
Gasket material:	Polyurethane		Ingress Protection (EN 60529): IP66/IP67	
Temperatures:			Impact Resistance (EN 62262): IK09	
Temperature °C (short term):	-40 ... 140 °C		Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 284 °F		UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F		Flammability Rating: UL 508	
Accessories:			Glow Wire Test (IEC 695-2-1) °C: 960	
ABP108	Painted Steel Back Panel		NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	

