



**Order symbol:** ARK864CHFTSSF  
**Product nbr:** 8561413  
**Description:** PC Enclosure  
**Remarks:** Hinged opaque flat cover w/S.S. Lockable twist latch, base includes 1/2 and 3/4 inch knock-outs and plastic mounting flanges.

**EAN:** 6418074095893  
**El. number:**  
**Finland:**

Sample photo

Including: Hinged cover. Base with 10-32 brass inserts, latched flat cover with formed in place PUR gasket, stainless hinge pin. Base with 1/2 and 3/4 inch knock-outs. Quick release latches. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	203	152	101	ALBP86	Aluminum Back Panel
<b>inch:</b>	8.0	6.0	4.0	ADFP86	Dead Front Panel w/ screws
<b>Materials:</b>				ASP86	Aluminum Swing Panel
<b>Material:</b>	Polycarbonate			ASPK86	Swing Panel Kit incl. Panel
<b>Base colour:</b>	RAL 7035 -light grey			ASPHK8	Swing Panel Kit w/o Panel
<b>Cover screws material:</b>	Stainless steel			AMFL6	6" Mounting Flange Set
<b>Cover colour:</b>	RAL 7035 -light grey			<b>Rating:</b>	
<b>Gasket material:</b>	Polyurethane			Ingress Protection (EN 60529): IP66/IP67	
<b>Temperatures:</b>				Impact Resistance (EN 62262): IK09	
<b>Temperature °C (short term):</b>	-40 ... 140 °C			Electrical insulation: Totally insulated	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Temperature °F (short term):</b>	-40 ... 284 °F			UV resistance: UL 508	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			Flammability Rating: UL 508	
<b>Accessories:</b>				Glow Wire Test (IEC 695-2-1) °C: 960	
ABP86	Painted Steel Back Panel			NEMA Class: NEMA 4, 4X, 6, 6P, 12, 13	
				<b>Certificates:</b>	
				Gost R	

