





Order Symbol: AR IPW 1210 BF

Description: Quarter Turn DIN Key, Opaque Flat Cover

## Remarks

Includes, cover and base with formed in place PUR gasket, mounting hardware and template for mounting frame

Dimensions	Length (metric)	Width inches (metric)	Height inches (metric)	Rating:
Inner Dimensions	11.42 (289.99)	9.49 (241.0)	2.31 (58.67)	NEMA 4, 4X,12 & 13

Outer Dimensions 13.46 (341.84) 11.62 (295.08) 2.45 (62.23)

Materials			Temperature		
Material:	Polycarbonate		Temperature C° (short term):	-40° -120° C"	
Base Color:	RAL 7035 - LIGHT GRAY		Temperature C° (continuous):	-40° - 80° C"	
Cover Color:	RAL 7035 - LIGHT GRAY		Temperature F° (short term):	-40° - 250° F	
Gasket material:	Polyurethane		Temperature F° (continuous):	-40° - 175° F	

