

Order symbol: ARK14127CHLTF
Product nbr: 8561584
Description: PC Enclosure
Remarks: Hinged transparent cover w/Plastic quick release latch. Base includes 1/2 and 3/4 inch knock-outs and plastic mounting flanges.

EAN: 6418074097606
EI. number:
Finland:

Including: Screw cover. Base with 10-32 brass inserts, cover with formed in place PUR gasket and 4 stainless cover screws. Base includes 1/2 and 3/4 inch knock-outs. Enclosure mounting foot kit. Accessory 10-32 screws for panel mounting.

Dimensions:				Accessories:	
Length	Width	Height			
mm:	356	305	178	ALBP1412	Aluminum Back Panel
inch:	14.0	12.0	7.0	ADFP1412	Dead Front Panel w/ screws
Materials:				ASP1412	Aluminum Swing Panel
Material:	Polycarbonate		ASPK1412	Swing Panel Kit incl. Panel	
Base colour:	RAL 7035 -light grey		ASPHK14	Swing Panel Kit w/o Panel	
Cover screws material:	Stainless steel		AMFL12	12" Mounting Flange Set	
Cover colour:	Clear transparent		Rating:		
Gasket material:	Polyurethane		Ingress Protection (EN 60529): IP66/IP67		
Temperatures:				Impact Resistance (EN 62262): IK09	
Temperature °C (short term):	-40 ... 140 °C		Electrical insulation: Totally insulated		
Temperature °C (continuous):	-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (short term):	-40 ... 284 °F		UV resistance: UL 508		
Temperature °F (continuous):	-40 ... 175 °F		Flammability Rating: UL 508		
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
ABP1412	Painted Steel Back Panel		NEMA Class: UL Type 4, 4X, 6, 6P, 12 and 13		

